$seem \ 2^{^{\mathsf{TM}}} led \ \mathsf{mud\text{-}in\ drywall}$ FSM2L-XF





▲ LUMINAIRE MUST BE INSTALLED PRIOR TO DRYWALL. ▲


KEY

CONFIGURATIONS ARE RUN SPECIFIC, PLEASE CONSULT FACTORY DRAWINGS BEFORE BEGINNING INSTALLATION.











DDVWALL













THICKNESS	ORIENTATION	GUIDE POINT	POSITION
3/8"	1	X	F
1/2"	1	X	Е
5/8"	1	X	D
3/4"	1	X	С
7/8"	1	Х	В
1"	1	X	Α
11/8"	1	Υ	G
11/4"	2	Υ	F
13/8"	2	Υ	E
11/2"	2	Υ	D
1 ⁵ /8"	2	Υ	С
13/4"	2	Υ	В
17/8"	2	Υ	Α
2"	2	Х	E
21/8"	2	Х	D



CEILING INSTALLATION (SEE PAGE 4 FOR WALL INSTALLATION)










3 USING THE BACKER FLANGE
PLACEMENT GUIDE FROM
PAGE 1 DETERMINE THE
PROPER PLACEMENT OF THE
BACKER FLANGE FOR YOUR
DRYWALL THICKNESS.

IF BACKER FLANGES WERE PRE-INSTALLED SKIP TO STEP 5













INDIVIDUAL INSTALLATIONS SKIP TO STEP 10










MAKE ELECTRICAL CONNECTION

















FLUSH LENS






POP-DOWN LENS



POP-DOWN LENS




WALL INSTALLATION






2"x6" FRAMING REQUIRED ON BOTH SIDES OF OF HOUSING




2 USING THE BACKER FLANGE
PLACEMENT GUIDE FROM
PAGE 1 DETERMINE THE
PROPER PLACEMENT OF THE
BACKER FLANGE FOR YOUR


IF BACKER FLANGES WERE PRE-INSTALLED SKIP TO STEP 4

DRYWALL THICKNESS.













INDIVIDUAL INSTALLATIONS SKIP TO STEP 9





























FLUSH LENS







POP-DOWN LENS





POP-DOWN LENS



DRIVER SERVICE







EMERGENCY



SEE BATTERY MANUFACTURER INSTRUCTIONS

EMERGENCY MAXIMUM MOUNTING HEIGHT: 19.00'